



ergolastec oil

THE MAT, RESISTANT TO OIL, GREASE AND GASOLINE













ergolastec oil

THE MAT, RESISTANT TO OIL, GREASE AND GASOLINE

basic data	oil_dry	oil_wet	oil_diamond	oil_drain
Upper surface	flat structure	bubble-top	diamond structure	bubble-top with drains
Bottom side	shock-absorbing bubbles	shock-absorbing bubbles	shock-absorbing bubbles	shock-absorbing bubbles
Outer edge	20° bevelled	20° bevelled	20° bevelled	20° bevelled
Lenght/width/thickness	1350 x 1000 x 16 mm*	1350 x 1000 x 20 mm*	1350 x 1000 x 20 mm*	1350 x 1000 x 19 mm*
Weight	19 ± 1 kg	19,5 ± 1 kg	19,5 ± 1 kg	18 ± 1 kg
Hardness	55 ± 4 Shore A	55 ± 4 Shore A	55 ± 4 Shore A	55 ± 4 Shore A
Temperatur resistance	- 30°C to + 110°C	- 30°C to + 110°C	- 30°C to + 110°C	- 30°C bis + 110°C
Interlocking designs	Typ A to K	Typ A to K	Typ A to K	Typ A to K
Material	NBR	NBR	NBR	NBR
Colour	black	black	black	black
Fire protection Certification	Cfl-s2**	Cfl-s2**	Cfl-s2**	Cfl-s2**
Oil resistance	Resistant to usual natural and mineral oils, such as for example cooling lubricants, nonpolar solvents and usual cleaning products sold in retail shops in respect of the instruction of use ***			

- * Tolerances according to DIN ISO 3302-1M4;
- ** According to EN 13501 (resistant to flying sparks and welding beads)
- *** For the application of not listed materials, it is recommended to contact the manufacturer

- ERGOLASTEC oil is restistant to oil, grease and gasoline
- The mat for all high-footfall areas and standup workstations
- ERGOLASTEC oil front of workbenches, assembly benches, production lines, turning and milling machines, eg.
- Bevelled outside edges for reduced risk of stumbling
- Very firm and sturdy making it suitable as a base when using transportation equipment
- This mat is due to the choice of high quality material comperatively odour less and therefore good applicable at indoor- areas
- Cleaning of mat and floor facilitated by simple removal of mat
- Further information for application and handling you will find in our manuel under www.ergolastec.com/Download

